
Ceramic and hybrid ball bearings

Technical Information

Chemical Resistance	Si3N4	ZrO2	X105CrMo17 (AISI 440C)	
Hydrochloric acid HCI (dil.)	+	+	-	
Hydrochloric acid HCI (conc.)	+	(+)	-	
Nitric acid HNO3 (dil.)	+	+	+	
Nitric acid HNO3 (conc.)	+	(+)	+	
Sulphuric acid H2SO4 (dil.)	+	+	-	
Sulphuric acid H2SO4 (conc.)	+	(+)	-	
Phosphoric acid H3PO4	+	+	-	
Hydrofluoric acid HF	-	-	-	
Sodium hydroxide solutions NaOH	+	+	+	
Potassium hydroxide solutions KOH	+	+	+	
Sodium chloride NaCl	+	+	-	
Potassium chloride KCI	+	+	-	
Copper chloride CuCl2	+	+	-	

Chemical resistance of ceramic material compared to ball bearings made from high-quality martensitic stainless steel (AISI 440C)

Material properties		Si3N4	ZrO2	100Cr6	
Density	ρ	g/cm³	3,2	5,9-6,4	7,85
Hardness	HV10	N/mm²	> 1700	> 1300	700
Elasticity	Е	GPa	300	205	210
Thermal expansion coeffic	ient α	10 ⁻⁶ /K	3,2	10,2	11,5
Flexural strength	σ	_B N/mm ²	> 800	1000 - 1500	> 2500
Fracture toughness	_{IC} M	Pa m½	8	8 - 12	> 20
Heat conductivity	Κλ	W/m \cdot K	30 - 35	2	40 - 45
Specific elect. resistance	ρ	Ωm	1012	109	10-7 - 10-6
Grain size	d	μM	< 1	< 1	-



A comparison of hot hard, heat resistant bearing materials

The material characteristics of ceramic ball bearings allow them to be used with lubrication or dry-running. This makes them ideal for use in hygienic areas, the food and pharmaceutical industries as well as medical, clean room and vacuum environments. The open construction allows ceramic bearings to be easily cleaned and they are insensitive to high-pressure cleaning. Their special properties allow them to be used in autoclaves without special maintenance or maintenance intervals. Ceramic ball bearings have a number of advantages over metal bearings:

- Exceptionally smooth running characteristics due to very low friction
- Little or no maintenance (possible use with lubrication, minimal lubrication or dry-running)
- Lower wear leading to a longer service life
- Up to 60% lighter
- Very high chemical resistance
- Resistant to corrosion and pitting
- Insensitive to moisture
- Extremely hard and rigid
- Non-magnetic, no interaction with magnetic fields
- High temperature resistance, up to 1600°C, depending on version

Due to its special properties the preferred material for ceramic bearings is silicon nitride (Si3N4) which is light, extremely strong and wear-resistant. The inexpensive alternative is zirconium oxide (ZrO2). Moreover, its thermal expansion is similar to that of steel and it is exceptionally well-suited for use in hybrid bearings.

Hybrid bearings (stainless steel races, ceramic balls) are a technical and economical alternative in cases where steel bearings are no longer adequate and full ceramic bearings are too costly. Compared to full steel bearings they permit higher speeds, are lighter, and because they have lower friction and require less lubrication have a longer service life.